



Command Plus[™] Knee (THK-4PSSL)

Locked until metatarsal load with Sit-EZ[™], a smoother sitting motion.

Any Amputee experienced with another Mechanical Stance Phase Locking knee will prefer the Command Plus' Sit-EZ[™] feature which provides a smoother, safer sitting motion. There is no need for the common "half-step" backward to sit down!

Primary benefits:

- ✓ **Sit-EZ[™] natural sitting motion makes entering vehicles safer & easier.**
- ✓ At mid swing-phase, Leg Length is shortened providing increased toe-ground clearance. This drastically reduces both the chance of tripping as well as daily energy consumption.
- ✓ The Command Plus' Swing Phase Shortening also eliminates the need to shorten the pylon excessively to reduce your Patient's chance of tripping. Correct Leg Length promotes smoother gait and preserves lower back function long-term.
- ✓ High resistance Pneumatic "Hydraulic-Like" dampening provides more precise control of heel rise and full extension dampening.

Suggested K3 L-Codes*

L5816 L5840 L5845 L5848 L5850

(Frequently used for K2 Patients as well)

Suggested K2 L-Codes*

L5611* GL L5816 L5845 L5850**

(See Full Suggested Coding Statement on pg. 53)

Complete Info & Images @ daw-usa.com

Knee Specifications:

| | |
|-----------------------|--|
| Stock Number | THK-4PSSL |
| Functional Level | K3 / K2 |
| Amputation Level | TF or Hip Disarticulation |
| Weight Limit | 250lb (113kg) |
| Knee Weight | 2.25lb (1011g) |
| Construction Material | Highest Grade Aerospace Alloy |
| Build Height | (See Next Page) |
| Stability Controls | Polycentric Mechanical Stance Phase Lock & Stance Flexion Adjustment |
| Swing Controls | Separate Pneumatic Extension / Flexion Dampening & Extension Assist Adjustment |
| Maximum Flexion Angle | Approx. 180° |
| Proximal Connection | M6 Threaded 4-Hole (See Selector Chart, Next Page) |
| Distal Connection | 30mm Tube Clamp |
| Warranty | 2 years included, Upgrade for an Additional 3 Years |

Order Includes:

- 1x Practitioner's Manual**
- 1x Suggested L-Codes Letter**

Recommended Foot:



K3 Pro-Action[™] Foot w/ Multi-Axial Ankle

Full info on page 64

Recommended Rotator:




Lo-Pro Rotator[™]

Proximally Attach ANY 4-Hole Connector


Full info on page 82

Command Plus™ Knee

Proximal Attachments Selector Chart



Build Height



| STOCK | MATERIAL | FULL INFO |
|--------------------|----------|-----------|
| 1 TSC-T | A | Pg. 75 |
| 2 TSC-BX | AA | Pg. 73 |
| 3 GUPS-FLAM3PRROT | S | Pg. 74 |
| 4 GUPT-MLAM | T | Pg. 73 |
| 5 TGH-01 | C | Pg. 56 |
| 6 GUPT-F4H | T | Pg. 79 |
| 7 GUPT-F4HROT | T | Pg. 79 |
| 8 TTG-14 | C | Pg. 90 |
| 9 GUPT-M4H | T | Pg. 78 |
| 10 TKR-01 | A | Pg. 82 |
| 11 GUPT-FCLAMP-ANG | T | Pg. 84 |

| MATERIALS | ADJUSTABILITY |
|-------------------------|----------------|
| A = Aluminum Alloy | A = Angular |
| AA = Areospace Aluminum | R = Rotational |
| C = Carbon Graphite | S = Sliding |
| S = Stainless Steel | |
| T = Titanium | |